


VINYL IVCOORDINATES






DANDE
DN-007 Ecu



SKETCH
SC-017 Flax



SKETCH
SC-002 Chamois



CARESSA FR
CA-002 Butterscotch



CARESSA FR
CA-029 Ochre



VERONA
VA-009 Bittersweet



SKETCH
SC-011 Paprika



INTERLOCHEN
IN-005 Wildberry




ENTWINE
ET-002 Maize




SEQUENCE
SQ-002 Chamois



DANDE
DN-009 Ember




SKETCH
SC-009 Tangerine



CARESSA FR
CA-021 Red Pepper



DANDE
DN-000 Taupe




VERONA
VA-012 Butter




SKETCH
SC-019 Caramel



DANDE
DN-009 Ember



CARESSA FR
CA-019 Bittersweet



SEQUENCE
SQ-001 Cranberry



DANDE
DN-000 Taupe




DANDE
DN-002 Sunshine



INTERLOCHEN
IN-009 Penny



SEQUENCE
SQ-009 Copper




ENTWINE
ET-019 Saffron



VERONA
VA-011 Ruby



CARESSA FR
CA-041 Burgundy



DANDE
DN-002 Sunshine



CARESSA FR
CA-060 Caramel




VERONA
VA-019 Cordovan



CARESSA FR
CA-009 Red Clay



CARESSA FR
CA-031 Brick



VERONA
VA-005 Eggplant



ENTWINE
ET-017 Natural



VERONA
VA-017 Croissant



CARESSA FR
CA-044 Cadet



VERONA
VA-014 Caribbean



CARESSA FR
CA-074 Spa



DANDE
DN-014 Aqua



INTERLOCHEN
IN-003 Limeade



DANDE
DN-003 Patina



DANDE
DN-004 Cerulean



SKETCH
SC-014 Royal



SKETCH
SC-024 Mist



SKETCH
SC-013 Basil




SEQUENCE
SQ-014 Grotto



VERONA
VA-024 Seamist



CARESSA FR
CA-093 Bluegrass



CARESSA FR
CA-083 Wasabi



CARESSA FR
CA-063 Willow




SEQUENCE
SQ-004 Indigo




INTERLOCHEN
IN-004 Aegean



SEQUENCE
SQ-024 Horizon



ENTWINE
ET-004 Aquamarine



ENTWINE
ET-003 Basil



SEQUENCE
SQ-003 Avocado



CARESSA FR
CA-014 Admiral



VERONA
VA-004 Sapphire



CARESSA FR
CA-064 Cerulean



SKETCH
SC-023 Bluegrass



SKETCH
SC-003 Ivy



VERONA
VA-003 Fern



SEQUENCE
SQ-007 Ivory



CARESSA FR
CA-067 Ecru



INTERLOCHEN
IN-002 White Gold



ENTWINE
ET-007 Parchment



CARESSA FR
CA-012 Mojave



SEQUENCE
SQ-030 Driftwood



INTERLOCHEN
IN-007 Champagne



CARESSA FR
CA-007 Kilimanjaro



SEQUENCE
SQ-006 Pewter



VERONA
VA-007 Parchment



SEQUENCE
SQ-020 Toast



VERONA
VA-016 Taupe



ENTWINE
ET-016 Grey Mist



INTERLOCHEN
IN-017 Quartz



SKETCH
SC-016 Cliff




SEQUENCE
SQ-017 Flax




VERONA
VA-030 Saddle



ENTWINE
ET-010 Bark




CARESSA FR
CA-037 Papyrus



CARESSA FR
CA-046 Stone



ENTWINE
ET-006 Shadow



CARESSA FR
CA-047 Doe



SKETCH
SC-020 Chestnut



CARESSA FR
CA-040 Java



DANDE
DN-010 Latte



SEQUENCE
SQ-016 Silverado



DANDE
DN-006 Charcoal




SKETCH
SC-007 Ecru




INTERLOCHEN
IN-010 Umber



INTERLOCHEN
IN-000 Truffle



VERONA
VA-020 Weathered



DANDE - Repeat: 20.125" H, 20.125" V, Random Match



ENTWINE - Repeat: 10.5" H, 10" V

STAIN RESISTANCE - Caressa, Dande, Entwine, Sequence, Sketch, Verona

Stain Resistance per CFFA 141 (Determines the resistance of a fabric to staining when subjected to common house-hold stains and cleaning agents) - Class 5 (Excellent) rating:									
Butter	Blood	Coffee	Hair Spray	Iodine/Betadine	Ketchup	Lipstick	Liquid Foundation	Mascara	
Mayonnaise	Motor Oil	Salad Dressing	Soda	Soy Sauce	Suntan Lotion	Tea	Urine	Whiskey	

SPECIFIC TREATMENTS - Caressa, Dande, Entwine, Sequence, Sketch, Verona

Stain Resistant with Resilience^{SR} Abrasion Resistant Anti-Bacterial Anti-Microbial Sulfide Stain Resistant Mildew Resistant Bleach Cleanable

Resilience^{SR}
ENDURING PROTECTION

Resilience^{SR} represents the latest technology in Faux Leather and Vinyl Protection, enhancing performance where it is needed the most.

Stain Resistance: With proper care, materials treated with Resilience^{SR} can be easily cleaned and will guard against stains maintaining the desired surface appearance for years to come.

Anti-Microbial & Anti-Bacterial Protection: Products treated with Resilience^{SR} are engineered to inhibit bacterial growth, as well as fungus, mold and mildew spores, resulting in a more hygienic environment.

Abrasion Resistance: Resilience^{SR} provides additional wear properties and surface durability to any vinyl or faux leather, thereby increasing the life of the material.

Resilience^{SR} is not visible, and does not affect the hand of the material. **Resilience^{SR}** is engineered to last, even after repeated cleaning and wear. Specify **Resilience^{SR}** for the most demanding healthcare and hospitality applications.

Resilience^{SR} complies with ASTM G-21/CFFA 120 and AATCC 147/CFFA 300 inhibiting the growth of the following organisms:
Aspergillus Niger Penicillium Pinaphilum Chaetomium Globosum Trichoderma Virens Aureobasidium Pullulans Staphylococcus Aureus
Klebsiella Pneumoniae Salmonella Choleraesuis Pseudomonas Aeruginosa

SPECIFIC TREATMENTS - Interlochen

Ag SILVERGUARD[®] Interlochen is treated with the most advanced silver ion technology, **SILVERGUARD[®]**, providing a natural germ-fighting defense to help safeguard the consumer against odor and stain causing bacteria. When combined with **PERMABLOK^{3®}**, Spradling's patented stain-fighting and abrasion-resistant treatment, also featured in Interlochen, **SILVERGUARD[®]** delivers the ultimate performance solution.

PERMABLOK^{3®} ADVANCED VINYL PROTECTION Protective Finish Anti-fungal/Anti-Bacterial Protection Anti-Stain Finish/Easily Cleaned Anti-Static Slip Finish Urine Stain Resistant
Mildew Resistant Backing and Face Superior Disinfectant Resistance Oil Resistant Sulfide Stain Resistant/All Colors UV Stabilized Pigments

PERMABLOK^{3®} ADVANCED VINYL PROTECTION is a proven vinyl protective coating that's engineered to create a tough effective barrier against germs, stains and surface abrasion, three of the biggest problems encountered in today's commercial environments.

CARE AND CLEANING INFORMATION - Caressa, Dande, Entwine, Sequence, Sketch, Verona

WS: Water/Solvent Cleaner – Spot clean, with a mild solvent, an upholstery shampoo, or the foam from a mild detergent. When using a solvent or dry cleaning product, follow instructions carefully and clean only in a well-ventilated room. Avoid any product that contains carbon tetrachloride or other toxic materials. With either method, pretest a small area before proceeding.

BC: Bleach Cleanable - 1 part bleach, 9 parts water = 10% bleach, 90% water solution. Always rinse promptly with clean water after applying the bleach solution.

Prompt cleaning is always recommended. Recommended cleaning steps are listed by type of stain. For best results follow steps in order.

Recommended Care and Cleaning Steps

- Step 1: Mild soap and water, then rinse with fresh water and wipe dry with a clean cloth.
Step 2: Wipe affected area with a soft cloth or soft bristle brush using a non-abrasive cleaner, i.e. Formula 409 or Fantastik. Rinse with fresh water and wipe dry.
Step 3: 10% solution of household bleach and water. Rinse with fresh water and wipe dry.
Step 4: 25% solution of alcohol and water. Rinse with fresh water and wipe dry.
Step 5: 25% solution of lighter fluid or nail polish remover and water. Rinse with fresh water and wipe dry.

*NOTE: The use of commercial vinyl conditioners and protectants is NOT RECOMMENDED.
The information in this cleaning guide refers to performance of Resilience in tests conducted under laboratory conditions. This information does not imply a specific guarantee and does not relieve the user from the responsibility of the proper and safe use of the product and referenced cleaning agents.*

CARE AND CLEANING INFORMATION - Interlochen

Remove stains with one of the following steps:

- Step 1 (eye shadow, mascara, grease, black felt tip pen, crayon, chocolate, suntan lotion, hair and body oils*): Remove excess spill with a damp cloth. Clean with a 1:1 mix of Ivory[®] liquid soap and water. Next, rinse with clean water and dry.
Step 2 (red lipstick): Use a straight application of concentrated cleaners such as Formula 409[®] or Fantastik[®] spray cleaner. Wipe with a clean cloth, rinse with clean water, and dry.
Step 3 (blood, urine, feces, oil base paint, tar and asphalt): Use a 1:1 mix of ammonia and water, or a 1:4 mix of bleach and water. Rinse with clean water and dry.
Steps 4 & 5 (all other tough stains): Step 4: Use a straight application of naphtha (lighter fluid). Rinse thoroughly with clean water and pat surface dry. Step 5: Use a 1:1 mix of isopropyl alcohol and water. If the stain persists, use straight alcohol. Rinse thoroughly with clean water and pat dry.
Note: For cleaning that requires step 4 or 5, use a soft cotton cloth saturated with the cleaning material and rub the stain in circles 10 times. Pat dry with another soft cotton cloth and check the results.
Please refer to the Mayer Fabrics website or contact customer service for approval of unlisted cleaning agents prior to use.

*Must be cleaned after each instance of exposure to hair and body oils.
The information published in this care guide refers to the performance of PERMABLOK^{3®} products in specific tests conducted under laboratory conditions. Results may vary under actual conditions.
This information is not a guarantee and does not relieve the user from the responsibility of the proper and safe use of the product and all cleaning agents. The use of certain agents can be harmful to the surface appearance and lifespan of vinyl.
Mayer Fabrics, its agents, and assigns assume no responsibility resulting from the use of such cleaning agents to the vinyl.
Please check compatibility when using this product in combination with painted or varnished surfaces.
PERMABLOK^{3®} is a registered trademark of Spradling Holdings, Inc.
Ivory[®] is a registered trademark of Procter and Gamble.
Formula 409[®] is a registered trademark of The Clorox Company.
Fantastik[®] is a registered trademark of DowBrands, Inc.
Mayer Fabrics is not sponsored by, affiliated with, or endorsed by such trademark owners. Additionally, any use by Mayer Fabrics of any third-party trademark does not constitute any endorsement by Mayer Fabrics of such third party.

TECHNICAL INFORMATION

Vinyl IV Coordinates

*Certification Marks Owned by ACT.

Pattern 54"	Content and Backing	GREENGUARD Certified	Weight/ Linear Yd	Pattern Repeat	Finish	Abrasion  Wyzenbeek	Light  Fastness	Flammability 	Cleaning Code
CARESSA FR	100% Vinyl Backing: 100% Polyester	Certified	29 oz.	None	Resilience ^{SR}	650,000 Double Rubs	1,000 hours	See below	WS, BC
DANDE <i>Directional</i>	100% Vinyl Backing: 100% Brushed Polyester Knit	Certified	30 oz.	20.125" H 20.125" V Random Match	Resilience ^{SR}	350,000 Double Rubs	500 hours	See below	WS, BC
ENTWINE <i>Directional</i>	100% Vinyl Backing: 100% Brushed Polyester Knit	Certified	30 oz.	10.5" H 10" V	Resilience ^{SR}	350,000 Double Rubs	500 hours	See below	WS, BC
INTERLOCHEN FR <i>Directional</i>	100% Vinyl 100% Hi-Loft™ Polyester	Certified	30 oz.	0.625" H 0.625" V	SILVERGUARD® with Antimicrobial Silver Ion Technology and PERMABLOK ³ ®	1,155,000 Double Rubs	1,000 hours	See below	Refer to cleaning section, BC
SEQUENCE <i>Directional</i>	100% Vinyl Backing: 100% Brushed Polyester Knit	Certified	30 oz.	1.5" H 1.5" V	Resilience ^{SR}	350,000 Double Rubs	500 hours	See below	WS, BC
SKETCH <i>Directional</i>	100% Vinyl Backing: 100% Polyester	Certified	32 oz.	Non-Matching	Resilience ^{SR}	1,150,000 Double Rubs	650 hours	See below	WS, BC
VERONA	100% Vinyl Backing: 100% Brushed Polyester Knit	Certified	32 oz.	None	Resilience ^{SR}	740,000 Double Rubs	650 hours	See below	WS, BC

All patterns may comply with California Technical Bulletin 133 when combined with appropriate components.

REDUCED ENVIRONMENTAL IMPACT

GREENGUARD Certified products are tested for low chemical emissions to standard UL 2818. For more information, visit UL.com/gg.

FLAMMABILITY

Caressa, Dande, Entwine, Interlochen, Sequence, Sketch, Verona

California Technical Bulletin 117-2013	Passes
California Technical Bulletin 117, Section E	Passes
NFPA 260 (Equivalent to UFAC) Class 1	Passes
FMVSS 302	Passes
IMO A.652 (16) 8.2 & 8.3 / IMO FTP 2010 Code MSC.307(88) Part 8, 3.1 & 3.2	Passes

Caressa, Dande, Entwine, Sequence, Sketch, Verona

ASTM E84 (Adhered) Class 1 or A	Passes
BIFMA	Passes

Caressa, Interlochen

Boston Fire Dept Code (BFD IX-1)	Passes
NY/NJ Port Authority	Passes

Interlochen

FAA/FAR 25.853(a)	Passes
-------------------	--------

ADDITIONAL INFORMATION

Additional colors are available. Please refer to the Mayer Fabrics website or contact customer service.

Custom Capabilities: All patterns can be custom colored. Minimum yardage applies.

Memo Samples: Please keep this card intact. Individual memo samples can be ordered on our website or by contacting customer service.

Fabric Color Matching: Mayer Fabrics always attempts to ship a satisfactory commercial match. Because of industry standard dye lot variation, colors may not match exactly.

Digital Swatch Card Color Matching: Due to color variations on different monitors and color printers, actual swatch colors may vary slightly. Please request a memo sample from Mayer Fabrics to ensure proper color representation.

Specifications: Specifications are correct at the time of printing. Additional specifications are available on our website.

For information or assistance with products or services, call us at 800.428.4415 or refer to our website, www.mayerfabrics.com.



GSA Contract #GS-28F-0022P



☎ 317.267.2626 or 800.428.4415 ☎ 317.267.2629 or 877.7SAMPLE

www.mayerfabrics.com
©2014 Mayer-Paetz, Inc.

VIN4CD  50914